

## **Product details**

DELfil – TR1: Compostable compound for transparent film

Applications: Fully Transparent Garment bags, hand gloves, shoe

cover & related products

Suitable for: Extrusion blown film (monolayer & multi-layer)



# **Properties**

Properties	Standard	Unit	Value
MFR (190°C/2.16 kg)	ASTM D 1238	g/10 min	2-4
Specific gravity	ASTM D 792	g/cm³	1.25
Tensile strength	ASTM D 882	MPa	30-40
Tensile Elongation	ASTM D 882	%	>150
Dart Impact	ASTM D 1709	gm	250-300
Melt point	ASTM D 3418	°C	120-160
Heat deflection temperature	ASTM D 648	°C	65

The values listed have been established on standardized test specimens at standard temperature and humidity conditions. It is valid only for Deltora's material in their original packing. It should not be mixed with any foreign material except recommended masterbatches by Deltora.

It should be stored in a dry and closed environment in their original packing. The shelf life is 6-8 months, when it is stored in its original packing, at room temperature and closed room environment. If the material is kept open to direct sunlight, moist/humid environment or high temperature; it can influence the material quality significantly. It should be open at the time of use only and should be used immediately.

The figures should be regarded as guide values only and it is based on our trial results and knowledge. Under certain conditions, the properties can be influenced to a significant extent by the processing conditions. This information does not exempt processors and users from their responsibility to conduct their own testing and inspections for each specific case. This information cannot be used to make a legally binding assurance about certain qualities for a specific unique case. Please contact us before starting production for more details about processing and for any customization.





Plot no. 7, Vraj industrial park, Inside Pirana gate, Ode village, SP Ring road, Ahmedabad 382427, India

Phone: +91 99988 96990

Email: info@deltorabiopolymers.com
Website: www.thebiopolymers.com;
www.deltorabiopolymers.com



# **Processing recommendations**

#### **Drving**:

- It should be pre-dried on hot air dryer at 65-70°C for 2-3 hours before using it.
- In case the product becomes too humid, drying at 55-60°C for 4 h by using a vacuum dryer or purging with dry air.

#### **Equipment:**

• Our materials are designed for standard equipment.

#### Start-up:

- Purge with polyolefin before starting production.
- Set the temperature to recommended settings before starting the production.
- · Never start with higher temperatures, it may burn and produce fumes rapidly, may cause harm to machine.

### Safety precautions:

- Processing at a melt temperature not higher than 190 °C.
- Processing with adequate ventilation.

#### Handling:

- Keep package sealed until use.
- · Reseal opened package directly after use.

### Interruption & shut-down:

- Never leave the material in the barrel for a longer period.
- By interruption for a considerable time, the material may get burn; purge out all the material from the barrel.
- If the material kept for a longer period in the barrel, purge with polyolefin and follow again start-up procedure.

# Temperature profile

Grade	Air Temperature	Die & Die Head	Screen Changer & Rotating Die	Zone 4	Zone 3	Zone 2	Zone 1 (Towards Feed zone)
DELfil – TR1	4-6 °C	152–155°C	148–150°C	150–155°C	145–150°C	145-150°C	140–145 °C





Plot no. 7, Vraj industrial park, Inside Pirana gate, Ode village, SP Ring road, Ahmedabad 382427, India

Phone: +91 99988 96990

Email: <a href="mailto:info@deltorabiopolymers.com">info@deltorabiopolymers.com</a>;
<a href="mailto:www.thebiopolymers.com">www.thebiopolymers.com</a>;
<a href="mailto:www.thebiopolymers.com">www.deltorabiopolymers.com</a>;
<a href="mailto:www.thebiopolymers.com">www.deltorabiopolymers.com</a>;